

Keysight Technologies

N2884A InfiniiMax Differential Fine-wire Probing Tip

Data Sheet




Figure 1: N2884A fine wire probing tip

Introduction

The N2884A InfiniiMax differential fine-wire probing tip is a high fidelity, high bandwidth solution to probe an active IC. It is targeted for R&D and test engineers using an oscilloscope for debugging and testing ICs. The N2884A provides an innovative differential probing approach that is unmatched by any competitors in the market.

Leveraging Keysight Technologies, Inc. low-cost ZIF probe head technology, the N2884A is designed to offer you a flat frequency response over the entire 12 GHz bandwidth specification, which eliminates the distortion and loading that affect probes with in-band resonance. Unlike other market solutions which measure a voltage versus some ground far away from the probe point, the N2884A measures a voltage versus an adjacent local ground (or other node) on the DUT.

- Bandwidth : 12 GHz (with 1169A InfiniiMax amplifier and N5425A ZIF probe head)
- Rise time : 33 psec (probe only)
- Input capacitance : 350 fF (differential), 520 fF (single-ended)
- Tungsten probing wire shaft diameter: 22 microns
- Point radius : <0.1 micron
- 100 mil long tungsten wires

The N2884A comes with a probe arm and a set of 5 probe tips. The probe arm is compatible with the Wentworth Laboratories micropositioner as shown in figure 3. You can either order it directly from Wentworth Laboratories (www.wentworthlab.com) or you can order it from Keysight. If you order it through Keysight, you must order the following two parts.

- N2884-64702 (Wentworth 2026-90409 PVX 400-M: Manual Linear Manipulator Magnetic Base)
- N2884-64703 (Wentworth 5-00-4711 Short Nose Articulated Short Arm Front)



Figure 2: N2884A comes with a probe arm and a set of 5 probe tips

To operate the wafer probing with N2884A, the following list of equipment is needed.

- Keysight Infiniium 9000, 80000 or 90000 Series oscilloscope
- N2884A InfiniiMax finewire probe tips
- 1130A-34A or 1168A/69A
- InfiniiMax probe amplifier
- N5425A ZIF probe head
- Wentworth micropositioner (can be orderable from Keysight)



Figure 3: N2884A with Wentworth micropositioner



Figure 4: Probe tips successfully landed on the test points

Measurement Plots




Figure 5: The step responses with (blue) and without (red) phase correction




Figure 6: The frequency characteristics of V_{out}/V_{in} with a $25\ \Omega$ source




Figure 7: The frequency response when two inputs are driven in common (common mode rejection)




Figure 8: The magnitude plot of probe input impedance vs. frequency

myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.



www.axiestandard.org

AdvancedTCA® Extensions for Instrumentation and Test (AXIe) is an open standard that extends the AdvancedTCA for general purpose and semiconductor test. Keysight is a founding member of the AXIe consortium. ATCA®, AdvancedTCA®, and the ATCA logo are registered US trademarks of the PCI Industrial Computer Manufacturers Group.



www.lxistandard.org

LAN eXtensions for Instruments puts the power of Ethernet and the Web inside your test systems. Keysight is a founding member of the LXI consortium.



www.pxisa.org

PCI eXtensions for Instrumentation (PXI) modular instrumentation delivers a rugged, PC-based high-performance measurement and automation system.



Three-Year Warranty

www.keysight.com/find/ThreeYearWarranty

Keysight's commitment to superior product quality and lower total cost of ownership. The only test and measurement company with three-year warranty standard on all instruments, worldwide.



Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to five years of protection and no budgetary surprises to ensure your instruments are operating to specification so you can rely on accurate measurements.



www.keysight.com/quality

Keysight Technologies, Inc.
DEKRA Certified ISO 9001:2008
Quality Management System

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

www.keysight.com/find/scope_probes

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	0800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:
www.keysight.com/find/contactus
(BP-07-10-14)